

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271188

Luminaire Tested: P3AS05R159827DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159827DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 98CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 161.1 lumens
Efficiency: N/A
Efficacy: 22.4 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271188

CATALOG NUMBER: P3AS05R159827DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1271188

CATALOG NUMBER: P3AS05R159827DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	105	99	94	90	102	97	92	89	94	90	87		91	87	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	88	78	72	67	86	77	71	67	76	70	66		74	69	65		72
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60258
5°	55338
10°	44087
15°	32940
20°	25016
25°	18945
30°	14027
35°	10012
40°	6841
45°	4807
50°	4094
55°	4014
60°	4166
65°	4410
70°	4488
75°	4660
80°	5051
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 5880 cd/sqm

TEST NUMBER: P1271188

CATALOG NUMBER: P3AS05R159827DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.3	13.8
10°-20°	40.7	25.3
20°-30°	36.1	22.4
30°-40°	23.6	14.7
40°-50°	12.6	7.9
50°-60°	9.6	5.9
60°-70°	8.2	5.1
70°-80°	5.7	3.5
80°-90°	2.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	99.0	61.5
0°-40°	122.7	76.1
0°-60°	144.9	89.9
0°-90°	161.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	161.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	275	
5°	251	22
15°	145	41
25°	78	36
35°	37	24
45°	16	13
55°	10	10
65°	8	8
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1271188

CATALOG NUMBER: P3AS05R159827DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	274.8
2.5°	268.3
5°	251.4
7.5°	226.4
10°	198.0
12.5°	170.6
15°	145.1
17.5°	124.7
20°	107.2
22.5°	91.8
25°	78.3
27.5°	66.3
30°	55.4
32.5°	45.9
35°	37.4
37.5°	29.9
40°	23.9
42.5°	19.0
45°	15.5
47.5°	13.5
50°	12.0
52.5°	11.5
55°	10.5
57.5°	10.0
60°	9.5
62.5°	9.0
65°	8.5
67.5°	7.5
70°	7.0
72.5°	6.0
75°	5.5
77.5°	4.5
80°	4.0
82.5°	3.5
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)