

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271999

Luminaire Tested: P3AS13R409827DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409827DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 949.1 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271999
CATALOG NUMBER: P3AS13R409827DE010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1271999

CATALOG NUMBER: P3AS13R409827DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96				96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92				92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89				89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85				85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82				82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79				79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76				76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73				73
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71				71
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69				69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	499675
5°	497269
10°	481064
15°	425610
20°	277691
25°	98377
30°	20864
35°	6880
40°	2519
45°	837
50°	682
55°	765
60°	614
65°	726
70°	449
75°	593
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 1176 cd/sqm



TEST NUMBER: P1271999
 CATALOG NUMBER: P3AS13R409827DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.6	22.4
10°-20°	495.0	52.2
20°-30°	214.8	22.6
30°-40°	19.8	2.1
40°-50°	2.8	0.3
50°-60°	1.7	0.2
60°-70°	1.3	0.1
70°-80°	0.7	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.4	97.2
0°-40°	942.2	99.3
0°-60°	946.7	99.8
0°-90°	949.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	949.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2279	
5°	2259	213
15°	1875	495
25°	407	215
35°	26	20
45°	3	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1271999
CATALOG NUMBER: P3AS13R409827DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2278.7
2.5°	2276.0
5°	2259.1
7.5°	2223.3
10°	2160.5
12.5°	2054.5
15°	1874.8
17.5°	1577.0
20°	1190.0
22.5°	772.6
25°	406.6
27.5°	174.9
30°	82.4
32.5°	44.6
35°	25.7
37.5°	15.5
40°	8.8
42.5°	4.7
45°	2.7
47.5°	2.0
50°	2.0
52.5°	2.0
55°	2.0
57.5°	2.0
60°	1.4
62.5°	1.4
65°	1.4
67.5°	1.4
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)