

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271200

Luminaire Tested: P3AS05R209827DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209827DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 175.0 lumens
Efficiency: N/A
Efficacy: 24.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271200

CATALOG NUMBER: P3AS05R209827DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271200

CATALOG NUMBER: P3AS05R209827DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134638
5°	122386
10°	90446
15°	55959
20°	31946
25°	18243
30°	10229
35°	5568
40°	3063
45°	1675
50°	989
55°	726
60°	658
65°	623
70°	513
75°	593
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1675 cd/sqm

TEST NUMBER: P1271200

CATALOG NUMBER: P3AS05R209827DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	27.5
10°-20°	68.7	39.3
20°-30°	35.9	20.5
30°-40°	13.9	7.9
40°-50°	4.5	2.6
50°-60°	1.8	1.0
60°-70°	1.2	0.7
70°-80°	0.7	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	152.7	87.3
0°-40°	166.6	95.2
0°-60°	172.9	98.8
0°-90°	175.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	175.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	614	
5°	556	48
15°	246	69
25°	75	36
35°	21	14
45°	5	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271200

CATALOG NUMBER: P3AS05R209827DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	614.0
1°	612.8
2°	605.6
3°	594.4
4°	577.2
5°	556.0
6°	531.0
7°	503.3
8°	471.2
9°	439.9
10°	406.2
12.5°	322.9
15°	246.5
17.5°	184.4
20°	136.9
22.5°	101.4
25°	75.4
27.5°	55.6
30°	40.4
32.5°	29.2
35°	20.8
37.5°	15.0
40°	10.7
42.5°	7.6
45°	5.4
47.5°	3.9
50°	2.9
52.5°	2.2
55°	1.9
57.5°	1.7
60°	1.5
62.5°	1.4
65°	1.2
67.5°	1.0
70°	0.8
72.5°	0.8
75°	0.7
77.5°	0.5
80°	0.3
82.5°	0.3
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)