

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271235

Luminaire Tested: P3AS05R259827DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271235
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259827DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 277.0 lumens
Efficiency: N/A
Efficacy: 38.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271235
CATALOG NUMBER: P3AS05R259827DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1271235
 CATALOG NUMBER: P3AS05R259827DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.1	9.8
10°-20°	64.9	23.4
20°-30°	73.3	26.5
30°-40°	58.0	20.9
40°-50°	29.3	10.6
50°-60°	11.7	4.2
60°-70°	7.5	2.7
70°-80°	4.1	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.2	59.6
0°-40°	223.2	80.6
0°-60°	264.2	95.4
0°-90°	277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	300	
5°	292	27
15°	234	65
25°	160	73
35°	93	58
45°	37	29
55°	12	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1271235
CATALOG NUMBER: P3AS05R259827DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	300.2
1°	300.2
2°	299.2
3°	297.5
4°	295.0
5°	291.9
6°	288.1
7°	283.7
8°	278.8
9°	273.3
10°	267.4
11°	260.9
12°	254.7
13°	247.4
14°	240.5
15°	233.6
17.5°	214.3
20°	195.3
22.5°	177.4
25°	160.1
27.5°	143.2
30°	126.0
32.5°	109.7
35°	92.8
37.5°	77.3
40°	62.5
42.5°	48.7
45°	36.6
47.5°	27.3
50°	19.7
52.5°	14.8
55°	12.1
57.5°	11.0
60°	9.7
62.5°	8.6
65°	7.6
67.5°	6.6
70°	5.5
72.5°	4.8
75°	3.8
77.5°	3.1
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.3



TEST NUMBER: P1271235
CATALOG NUMBER: P3AS05R259827DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)