

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271236

Luminaire Tested: P3AS05R259827DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259827DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 277.0 lumens
Efficiency: N/A
Efficacy: 38.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271236

CATALOG NUMBER: P3AS05R259827DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1271236

CATALOG NUMBER: P3AS05R259827DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65828
5°	64253
10°	59540
15°	53031
20°	45574
25°	38736
30°	31904
35°	24842
40°	17891
45°	11350
50°	6720
55°	4626
60°	4254
65°	3943
70°	3526
75°	3219
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11350 cd/sqm

TEST NUMBER: P1271236

CATALOG NUMBER: P3AS05R259827DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.1	9.8
10°-20°	64.9	23.4
20°-30°	73.3	26.5
30°-40°	58.0	20.9
40°-50°	29.3	10.6
50°-60°	11.7	4.2
60°-70°	7.5	2.7
70°-80°	4.1	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.2	59.6
0°-40°	223.2	80.6
0°-60°	264.2	95.4
0°-90°	277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	300	
5°	292	27
15°	234	65
25°	160	73
35°	93	58
45°	37	29
55°	12	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1271236

CATALOG NUMBER: P3AS05R259827DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	300.2
1°	300.2
2°	299.2
3°	297.5
4°	295.0
5°	291.9
6°	288.1
7°	283.7
8°	278.8
9°	273.3
10°	267.4
11°	260.9
12°	254.7
13°	247.4
14°	240.5
15°	233.6
17.5°	214.3
20°	195.3
22.5°	177.4
25°	160.1
27.5°	143.2
30°	126.0
32.5°	109.7
35°	92.8
37.5°	77.3
40°	62.5
42.5°	48.7
45°	36.6
47.5°	27.3
50°	19.7
52.5°	14.8
55°	12.1
57.5°	11.0
60°	9.7
62.5°	8.6
65°	7.6
67.5°	6.6
70°	5.5
72.5°	4.8
75°	3.8
77.5°	3.1
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.3



TEST NUMBER: P1271236

CATALOG NUMBER: P3AS05R259827DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)