

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272048

Luminaire Tested: P3AS13R459827DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459827DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 487.1 lumens
Efficiency: N/A
Efficacy: 33.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272048

CATALOG NUMBER: P3AS13R459827DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1272048

CATALOG NUMBER: P3AS13R459827DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74		
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69		
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64		
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145054
5°	141756
10°	130770
15°	113712
20°	93411
25°	72682
30°	53679
35°	37771
40°	23587
45°	12777
50°	6925
55°	5926
60°	5350
65°	4566
70°	3911
75°	3982
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12777 cd/sqm

TEST NUMBER: P1272048

CATALOG NUMBER: P3AS13R459827DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.6	12.2
10°-20°	138.5	28.4
20°-30°	137.5	28.2
30°-40°	88.5	18.2
40°-50°	34.1	7.0
50°-60°	13.9	2.8
60°-70°	8.8	1.8
70°-80°	4.7	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.6	68.9
0°-40°	424.1	87.1
0°-60°	472.1	96.9
0°-90°	487.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	487.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	662	
5°	644	60
15°	501	138
25°	300	137
35°	141	89
45°	41	34
55°	16	14
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1272048

CATALOG NUMBER: P3AS13R459827DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	661.5
2.5°	658.1
5°	644.0
7.5°	619.7
10°	587.3
12.5°	546.8
15°	500.9
17.5°	450.9
20°	400.3
22.5°	349.0
25°	300.4
27.5°	254.5
30°	212.0
32.5°	174.8
35°	141.1
37.5°	110.7
40°	82.4
42.5°	59.4
45°	41.2
47.5°	27.7
50°	20.3
52.5°	16.9
55°	15.5
57.5°	13.5
60°	12.2
62.5°	10.1
65°	8.8
67.5°	7.4
70°	6.1
72.5°	5.4
75°	4.7
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)