

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272053

Luminaire Tested: P3AS13R509827DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272053
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509827DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 925.0 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272053

CATALOG NUMBER: P3AS13R509827DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1272053

CATALOG NUMBER: P3AS13R509827DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80		
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76		
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72		
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65		
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322145
5°	316376
10°	303780
15°	278571
20°	245651
25°	188285
30°	102370
35°	32926
40°	7729
45°	1054
50°	921
55°	1032
60°	877
65°	1038
70°	898
75°	1186
80°	884
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 1761 cd/sqm

TEST NUMBER: P1272053

CATALOG NUMBER: P3AS13R509827DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.9	14.6
10°-20°	341.1	36.9
20°-30°	341.6	36.9
30°-40°	96.0	10.4
40°-50°	5.8	0.6
50°-60°	2.2	0.2
60°-70°	1.8	0.2
70°-80°	1.2	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.6	88.4
0°-40°	913.6	98.8
0°-60°	921.6	99.6
0°-90°	925.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	925.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1469	
5°	1437	135
15°	1227	341
25°	778	342
35°	123	96
45°	3	6
55°	3	2
65°	2	2
75°	1	1
85°	1	0
90°	0	

TEST NUMBER: P1272053

CATALOG NUMBER: P3AS13R509827DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1469.1
2.5°	1461.7
5°	1437.3
7.5°	1404.2
10°	1364.3
12.5°	1304.2
15°	1227.1
17.5°	1138.5
20°	1052.7
22.5°	945.8
25°	778.2
27.5°	579.4
30°	404.3
32.5°	244.1
35°	123.0
37.5°	58.1
40°	27.0
42.5°	10.1
45°	3.4
47.5°	2.7
50°	2.7
52.5°	2.7
55°	2.7
57.5°	2.0
60°	2.0
62.5°	2.0
65°	2.0
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)