

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272057

Luminaire Tested: P3AS13R509827DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509827DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 939.0 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272057

CATALOG NUMBER: P3AS13R509827DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1272057

CATALOG NUMBER: P3AS13R509827DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	328154
5°	319414
10°	304804
15°	275938
20°	238721
25°	195810
30°	112498
35°	34934
40°	9389
45°	3287
50°	785
55°	268
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3287 cd/sqm

TEST NUMBER: P1272057

CATALOG NUMBER: P3AS13R509827DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.9	14.5
10°-20°	336.8	35.9
20°-30°	354.0	37.7
30°-40°	101.3	10.8
40°-50°	9.9	1.1
50°-60°	0.8	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	826.7	88.0
0°-40°	928.0	98.8
0°-60°	938.7	100.0
0°-90°	939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	939.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1496	
5°	1451	136
15°	1216	337
25°	809	354
35°	130	101
45°	11	10
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1272057

CATALOG NUMBER: P3AS13R509827DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1496.5
1°	1494.1
2°	1487.5
3°	1477.9
4°	1465.0
5°	1451.1
6°	1436.2
7°	1420.3
8°	1405.3
9°	1388.1
10°	1368.9
11°	1346.7
12°	1321.2
13°	1289.4
14°	1254.9
15°	1215.5
16°	1173.8
17°	1133.4
18°	1091.9
19°	1055.5
20°	1023.0
21°	991.9
22°	956.4
23°	915.7
24°	868.0
25°	809.3
26°	745.7
27°	674.8
28°	604.3
29°	528.1
30°	444.3
31°	365.7
32°	293.5
32.5°	262.1
33°	230.2
34°	176.6
35°	130.5
36°	95.7
37°	71.2
37.5°	61.6
38°	53.3
39°	41.4
40°	32.8
42.5°	18.6
45°	10.6



TEST NUMBER: P1272057

CATALOG NUMBER: P3AS13R509827DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.0
50°	2.3
52.5°	1.0
55°	0.7
57.5°	0.7
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)