

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271245

Luminaire Tested: P3AS05R259827DE010 E3PHLD1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1271245  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R259827DE010 E3PHLD1MW  
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 277.0 lumens  
Efficiency: N/A  
Efficacy: 38.5 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271245  
CATALOG NUMBER: P3AS05R259827DE010 E3PHLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1271245  
 CATALOG NUMBER: P3AS05R259827DE010 E3PHLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80	80	80	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72	72	72	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65	65	65	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	55	55	55	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50	50	50	50
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47	47	47	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	41	41	41	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72275
5°	68611
10°	59429
15°	48377
20°	38223
25°	30486
30°	24713
35°	20130
40°	16688
45°	14048
50°	11906
55°	10475
60°	9166
65°	7990
70°	7052
75°	5931
80°	4420
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14048 cd/sqm



TEST NUMBER: P1271245  
 CATALOG NUMBER: P3AS05R259827DE010 E3PHLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	28.3	10.2
10°-20°	59.1	21.3
20°-30°	58.2	21.0
30°-40°	47.4	17.1
40°-50°	35.2	12.7
50°-60°	24.6	8.9
60°-70°	15.4	5.5
70°-80°	7.4	2.7
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	145.6	52.6
0°-40°	193.1	69.7
0°-60°	252.8	91.3
0°-90°	277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	330	
5°	312	28
15°	213	59
25°	126	58
35°	75	47
45°	45	35
55°	27	25
65°	15	15
75°	7	7
85°	1	1
90°	0	



TEST NUMBER: P1271245  
CATALOG NUMBER: P3AS05R259827DE010 E3PHLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	329.6
2.5°	325.1
5°	311.7
7.5°	291.3
10°	266.9
12.5°	240.0
15°	213.1
17.5°	186.7
20°	163.8
22.5°	143.9
25°	126.0
27.5°	110.5
30°	97.6
32.5°	85.6
35°	75.2
37.5°	66.2
40°	58.3
42.5°	51.3
45°	45.3
47.5°	39.8
50°	34.9
52.5°	30.9
55°	27.4
57.5°	23.9
60°	20.9
62.5°	17.9
65°	15.4
67.5°	12.9
70°	11.0
72.5°	9.0
75°	7.0
77.5°	5.0
80°	3.5
82.5°	2.0
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)