

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272068

Luminaire Tested: P3AS13R509827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 290.0 lumens
Efficiency: N/A
Efficacy: 20.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272068

CATALOG NUMBER: P3AS13R509827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272068

CATALOG NUMBER: P3AS13R509827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58943
5°	58067
10°	55488
15°	51396
20°	46181
25°	40599
30°	34537
35°	28001
40°	21039
45°	13552
50°	6448
55°	5046
60°	4780
65°	4462
70°	4039
75°	3643
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13552 cd/sqm

TEST NUMBER: P1272068

CATALOG NUMBER: P3AS13R509827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.7	8.5
10°-20°	63.1	21.8
20°-30°	76.7	26.4
30°-40°	65.0	22.4
40°-50°	33.8	11.7
50°-60°	12.2	4.2
60°-70°	8.4	2.9
70°-80°	4.6	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.5	56.7
0°-40°	229.6	79.2
0°-60°	275.6	95.0
0°-90°	290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	290.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	269	
5°	264	25
15°	226	63
25°	168	77
35°	105	65
45°	44	34
55°	13	12
65°	9	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1272068

CATALOG NUMBER: P3AS13R509827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	268.8
2.5°	267.8
5°	263.8
7.5°	257.8
10°	249.2
12.5°	238.3
15°	226.4
17.5°	212.8
20°	197.9
22.5°	182.7
25°	167.8
27.5°	152.3
30°	136.4
32.5°	120.5
35°	104.6
37.5°	89.0
40°	73.5
42.5°	58.6
45°	43.7
47.5°	29.1
50°	18.9
52.5°	14.6
55°	13.2
57.5°	11.9
60°	10.9
62.5°	9.6
65°	8.6
67.5°	7.3
70°	6.3
72.5°	5.3
75°	4.3
77.5°	3.3
80°	2.6
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)