

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271249

Luminaire Tested: P3AS05R309827DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271249
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309827DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 438.9 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271249

CATALOG NUMBER: P3AS05R309827DE010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1271249

CATALOG NUMBER: P3AS05R309827DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	92	89	94	90	88		92	89	87		91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85		90	87	85		89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83		87	84	82		86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76		81	78	76		80	77	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	357493
5°	350736
10°	310482
15°	196709
20°	74673
25°	22114
30°	8736
35°	2677
40°	1174
45°	434
50°	341
55°	268
60°	307
65°	363
70°	192
75°	254
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 434 cd/sqm

TEST NUMBER: P1271249

CATALOG NUMBER: P3AS05R309827DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.5	33.4
10°-20°	228.3	52.0
20°-30°	53.0	12.1
30°-40°	8.2	1.9
40°-50°	1.4	0.3
50°-60°	0.7	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.8	97.5
0°-40°	436.0	99.3
0°-60°	438.0	99.8
0°-90°	438.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	438.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1630	
5°	1593	146
15°	866	228
25°	91	53
35°	10	8
45°	1	1
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1271249

CATALOG NUMBER: P3AS05R309827DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1630.3
1°	1629.3
2°	1624.8
3°	1617.2
4°	1607.5
5°	1593.4
6°	1575.8
7°	1549.6
8°	1513.8
9°	1461.0
10°	1394.4
11°	1308.6
12°	1211.7
13°	1104.1
14°	985.8
15°	866.5
17.5°	566.9
20°	320.0
22.5°	163.4
25°	91.4
27.5°	56.2
30°	34.5
32.5°	18.6
35°	10.0
37.5°	6.6
40°	4.1
42.5°	2.4
45°	1.4
47.5°	1.0
50°	1.0
52.5°	0.7
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1271249

CATALOG NUMBER: P3AS05R309827DE010 E3CB1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)