

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271253

Luminaire Tested: P3AS05R309827DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1271253  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R309827DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 435.0 lumens  
Efficiency: N/A  
Efficacy: 60.4 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271253

CATALOG NUMBER: P3AS05R309827DE010 E3D1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1271253

CATALOG NUMBER: P3AS05R309827DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 115 | 113 | 111 | 109 |  | 113 | 111 | 109 | 108 |  | 107 | 106 | 104 |  | 103 | 102 | 101 |  | 100 | 99  | 98  |
| 2   | 111 | 108 | 105 | 102 |  | 109 | 106 | 103 | 101 |  | 103 | 101 | 99  |  | 100 | 98  | 97  |  | 97  | 96  | 95  |
| 3   | 108 | 103 | 100 | 97  |  | 106 | 102 | 99  | 96  |  | 99  | 97  | 95  |  | 97  | 95  | 93  |  | 95  | 93  | 92  |
| 4   | 105 | 99  | 95  | 92  |  | 103 | 98  | 95  | 92  |  | 96  | 93  | 91  |  | 94  | 92  | 90  |  | 93  | 91  | 89  |
| 5   | 101 | 96  | 92  | 89  |  | 100 | 95  | 91  | 88  |  | 93  | 90  | 87  |  | 92  | 89  | 87  |  | 90  | 88  | 86  |
| 6   | 99  | 92  | 88  | 85  |  | 97  | 92  | 88  | 85  |  | 90  | 87  | 84  |  | 89  | 86  | 84  |  | 88  | 85  | 83  |
| 7   | 96  | 89  | 85  | 82  |  | 95  | 89  | 85  | 82  |  | 88  | 84  | 82  |  | 87  | 84  | 81  |  | 86  | 83  | 81  |
| 8   | 93  | 87  | 83  | 80  |  | 92  | 86  | 82  | 80  |  | 85  | 82  | 79  |  | 84  | 81  | 79  |  | 84  | 81  | 79  |
| 9   | 91  | 84  | 80  | 77  |  | 90  | 84  | 80  | 77  |  | 83  | 79  | 77  |  | 82  | 79  | 77  |  | 82  | 79  | 77  |
| 10  | 88  | 82  | 78  | 75  |  | 88  | 81  | 78  | 75  |  | 81  | 77  | 75  |  | 80  | 77  | 75  |  | 80  | 77  | 75  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 346091 |
| 5°  | 341580 |
| 10° | 298235 |
| 15° | 189558 |
| 20° | 75093  |
| 25° | 25090  |
| 30° | 11673  |
| 35° | 5300   |
| 40° | 2032   |
| 45° | 992    |
| 50° | 273    |
| 55° | 115    |
| 60° | 88     |
| 65° | 104    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 992 cd/sqm

TEST NUMBER: P1271253

CATALOG NUMBER: P3AS05R309827DE010 E3D1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 141.9  | 32.6      |
| 10°-20°   | 220.0  | 50.6      |
| 20°-30°   | 56.7   | 13.0      |
| 30°-40°   | 13.3   | 3.1       |
| 40°-50°   | 2.6    | 0.6       |
| 50°-60°   | 0.3    | 0.1       |
| 60°-70°   | 0.2    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 418.6  | 96.2      |
| 0°-40°    | 432.0  | 99.3      |
| 0°-60°    | 434.8  | 100.0     |
| 0°-90°    | 435.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 435.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1578 |      |
| 5°  | 1552 | 142  |
| 15° | 835  | 220  |
| 25° | 104  | 57   |
| 35° | 20   | 13   |
| 45° | 3    | 3    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1271253

CATALOG NUMBER: P3AS05R309827DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1578.3 |
| 1°    | 1577.2 |
| 2°    | 1573.4 |
| 3°    | 1569.2 |
| 4°    | 1563.0 |
| 5°    | 1551.8 |
| 6°    | 1533.8 |
| 7°    | 1503.7 |
| 8°    | 1462.7 |
| 9°    | 1409.1 |
| 10°   | 1339.4 |
| 11°   | 1256.5 |
| 12°   | 1166.0 |
| 13°   | 1061.8 |
| 14°   | 952.7  |
| 15°   | 835.0  |
| 16°   | 719.7  |
| 17°   | 608.6  |
| 18°   | 502.0  |
| 19°   | 404.3  |
| 20°   | 321.8  |
| 21°   | 253.3  |
| 22°   | 199.3  |
| 23°   | 157.7  |
| 24°   | 126.3  |
| 25°   | 103.7  |
| 26°   | 86.5   |
| 27°   | 73.5   |
| 28°   | 63.5   |
| 29°   | 54.4   |
| 30°   | 46.1   |
| 32.5° | 29.0   |
| 35°   | 19.8   |
| 37.5° | 12.3   |
| 40°   | 7.1    |
| 42.5° | 4.7    |
| 45°   | 3.2    |
| 47.5° | 1.9    |
| 50°   | 0.8    |
| 52.5° | 0.3    |
| 55°   | 0.3    |
| 57.5° | 0.2    |
| 60°   | 0.2    |
| 62.5° | 0.2    |
| 65°   | 0.2    |



TEST NUMBER: P1271253

CATALOG NUMBER: P3AS05R309827DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 0.2 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)