Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272076

Luminaire Tested: P3AS13R509827DE010 E3DLP1LI

Issue Date: 1/30/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1272076
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab:	INNOVATION CENTER
Issue Date:	1/30/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	IRiS
Catalog Number:	P3AS13R509827DE010 E3DLP1LI
Description:	3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DLP1LI TRIM
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	499.0 lumens
Efficiency:	N/A
Efficacy:	34.4 lumens/watt
Spacing Criteria (0/90/45):	0.75 / 0.75 / 0.77
Luminous Opening:	Circular (Dia: 0.25' x H: 0')
CIE Type:	Direct

Input Watts (W):	14.5
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1272076
CATALOG NUMBER: P3AS13R509827DE010 E3DLP1LI

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1272076
CATALOG NUMBER: P3AS13R509827DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145142
5°	141228
10°	130236
15°	114530
20°	95815
25°	75972
30°	55755
35°	38334
40°	24360
45°	13614
50°	7369
55°	6193
60°	5350
65°	4929
70°	4360
75°	3982
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 13614 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1272076
CATALOG NUMBER: P3AS13R509827DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.4	11.9
10°-20°	139.7	28.0
20°-30°	142.9	28.6
30°-40°	90.6	18.2
40°-50°	36.1	7.2
50°-60°	14.6	2.9
60°-70°	9.4	1.9
70°-80°	4.8	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	342.1	68.5
0°-40°	432.7	86.7
0°-60°	483.4	96.9
0°-90°	499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	662	
5°	642	59
15°	504	140
25°	314	143
35°	143	91
45°	44	36
55°	16	15
65°	10	9
75°	5	5
85°	1	1
90°	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1272076
CATALOG NUMBER: P3AS13R509827DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	661.9
2.5°	657.1
5°	641.6
7.5°	617.3
10°	584.9
12.5°	546.4
15°	504.5
17.5°	458.6
20°	410.6
22.5°	362.7
25°	314.0
27.5°	265.4
30°	220.2
32.5°	179.6
35°	143.2
37.5°	112.1
40°	85.1
42.5°	62.8
45°	43.9
47.5°	29.7
50°	21.6
52.5°	18.2
55°	16.2
57.5°	14.2
60°	12.2
62.5°	10.8
65°	9.5
67.5°	8.1
70°	6.8
72.5°	5.4
75°	4.7
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)