

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272108

Luminaire Tested: P3AS13R559827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272108
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 492.0 lumens
Efficiency: N/A
Efficacy: 33.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272108

CATALOG NUMBER: P3AS13R559827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1272108

CATALOG NUMBER: P3AS13R559827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133849
5°	130486
10°	121307
15°	108014
20°	91801
25°	74085
30°	56490
35°	40181
40°	26507
45°	15723
50°	9211
55°	5696
60°	5043
65°	4566
70°	3911
75°	3474
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15723 cd/sqm

TEST NUMBER: P1272108

CATALOG NUMBER: P3AS13R559827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	11.2
10°-20°	131.9	26.8
20°-30°	139.7	28.4
30°-40°	94.4	19.2
40°-50°	41.4	8.4
50°-60°	14.8	3.0
60°-70°	8.7	1.8
70°-80°	4.6	0.9
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.7	66.4
0°-40°	421.1	85.6
0°-60°	477.3	97.0
0°-90°	492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	610	
5°	593	55
15°	476	132
25°	306	140
35°	150	94
45°	51	41
55°	15	15
65°	9	9
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1272108

CATALOG NUMBER: P3AS13R559827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	610.4
2.5°	605.6
5°	592.8
7.5°	571.8
10°	544.8
12.5°	512.3
15°	475.8
17.5°	435.3
20°	393.4
22.5°	349.5
25°	306.2
27.5°	263.6
30°	223.1
32.5°	184.5
35°	150.1
37.5°	119.0
40°	92.6
42.5°	69.6
45°	50.7
47.5°	37.2
50°	27.0
52.5°	18.9
55°	14.9
57.5°	13.5
60°	11.5
62.5°	10.1
65°	8.8
67.5°	7.4
70°	6.1
72.5°	5.4
75°	4.1
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)