

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271264

Luminaire Tested: P3AS05R309827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 138.0 lumens
Efficiency: N/A
Efficacy: 19.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271264

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271264

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	77	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32607
5°	31873
10°	29637
15°	26379
20°	22682
25°	19211
30°	15952
35°	12501
40°	8960
45°	5892
50°	3343
55°	2217
60°	2061
65°	1920
70°	1731
75°	1610
80°	1515
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5892 cd/sqm

TEST NUMBER: P1271264

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.4	9.7
10°-20°	32.3	23.4
20°-30°	36.4	26.4
30°-40°	29.1	21.1
40°-50°	14.9	10.8
50°-60°	5.6	4.1
60°-70°	3.7	2.7
70°-80°	2.0	1.4
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	82.1	59.5
0°-40°	111.2	80.6
0°-60°	131.8	95.5
0°-90°	138.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	138.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	149	
5°	145	13
15°	116	32
25°	79	36
35°	47	29
45°	19	15
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1271264

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	148.7
1°	148.7
2°	148.2
3°	147.3
4°	146.1
5°	144.8
6°	143.1
7°	140.9
8°	138.5
9°	135.8
10°	133.1
11°	130.1
12°	126.8
13°	123.4
14°	119.9
15°	116.2
17.5°	106.7
20°	97.2
22.5°	88.1
25°	79.4
27.5°	71.0
30°	63.0
32.5°	54.9
35°	46.7
37.5°	38.8
40°	31.3
42.5°	24.7
45°	19.0
47.5°	14.1
50°	9.8
52.5°	6.9
55°	5.8
57.5°	5.2
60°	4.7
62.5°	4.2
65°	3.7
67.5°	3.2
70°	2.7
72.5°	2.2
75°	1.9
77.5°	1.5
80°	1.2
82.5°	0.8
85°	0.5
87.5°	0.2



TEST NUMBER: P1271264

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)