

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271265

Luminaire Tested: P3AS05R309827DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1271265  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R309827DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 281.0 lumens  
Efficiency: N/A  
Efficacy: 39.0 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271265

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1271265

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 89  |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 84  |
| 4   | 94  | 86  | 79  | 74  | 92  | 84  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 68  | 76  | 71  | 67  |  | 75  | 70  | 66  |  | 73  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 62  |  | 70  | 65  | 61  |  | 69  |
| 7   | 79  | 69  | 62  | 58  | 78  | 68  | 62  | 58  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 58  | 54  | 74  | 64  | 58  | 53  | 63  | 57  | 53  |  | 62  | 57  | 53  |  | 61  |
| 9   | 71  | 61  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 54  | 50  |  | 58  | 53  | 50  |  | 57  |
| 10  | 68  | 57  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 50  | 47  |  | 55  | 50  | 46  |  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 66376 |
| 5°  | 64891 |
| 10° | 60342 |
| 15° | 53689 |
| 20° | 46181 |
| 25° | 39123 |
| 30° | 32486 |
| 35° | 25484 |
| 40° | 18263 |
| 45° | 11970 |
| 50° | 6823  |
| 55° | 4473  |
| 60° | 4254  |
| 65° | 3943  |
| 70° | 3526  |
| 75° | 3219  |
| 80° | 3031  |
| 85° | 2516  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11970 cd/sqm

TEST NUMBER: P1271265

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 27.4   | 9.7       |
| 10°-20°   | 65.8   | 23.4      |
| 20°-30°   | 74.1   | 26.4      |
| 30°-40°   | 59.2   | 21.1      |
| 40°-50°   | 30.4   | 10.8      |
| 50°-60°   | 11.4   | 4.1       |
| 60°-70°   | 7.5    | 2.7       |
| 70°-80°   | 4.0    | 1.4       |
| 80°-90°   | 1.1    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 167.2  | 59.5      |
| 0°-40°    | 226.4  | 80.6      |
| 0°-60°    | 268.3  | 95.5      |
| 0°-90°    | 281.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 281.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 303 |      |
| 5°  | 295 | 27   |
| 15° | 236 | 66   |
| 25° | 162 | 74   |
| 35° | 95  | 59   |
| 45° | 39  | 30   |
| 55° | 12  | 11   |
| 65° | 8   | 8    |
| 75° | 4   | 4    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1271265

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 302.7 |
| 1°    | 302.7 |
| 2°    | 301.7 |
| 3°    | 300.0 |
| 4°    | 297.6 |
| 5°    | 294.8 |
| 6°    | 291.4 |
| 7°    | 286.9 |
| 8°    | 282.1 |
| 9°    | 276.5 |
| 10°   | 271.0 |
| 11°   | 264.8 |
| 12°   | 258.3 |
| 13°   | 251.4 |
| 14°   | 244.1 |
| 15°   | 236.5 |
| 17.5° | 217.2 |
| 20°   | 197.9 |
| 22.5° | 179.3 |
| 25°   | 161.7 |
| 27.5° | 144.5 |
| 30°   | 128.3 |
| 32.5° | 111.7 |
| 35°   | 95.2  |
| 37.5° | 79.0  |
| 40°   | 63.8  |
| 42.5° | 50.3  |
| 45°   | 38.6  |
| 47.5° | 28.6  |
| 50°   | 20.0  |
| 52.5° | 14.1  |
| 55°   | 11.7  |
| 57.5° | 10.7  |
| 60°   | 9.7   |
| 62.5° | 8.6   |
| 65°   | 7.6   |
| 67.5° | 6.6   |
| 70°   | 5.5   |
| 72.5° | 4.5   |
| 75°   | 3.8   |
| 77.5° | 3.1   |
| 80°   | 2.4   |
| 82.5° | 1.7   |
| 85°   | 1.0   |
| 87.5° | 0.3   |



TEST NUMBER: P1271265

CATALOG NUMBER: P3AS05R309827DE010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)