

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271270

Luminaire Tested: P3AS05R309827DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271270
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309827DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 109.0 lumens
Efficiency: N/A
Efficacy: 15.1 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271270
CATALOG NUMBER: P3AS05R309827DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1271270
 CATALOG NUMBER: P3AS05R309827DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	68	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37256
5°	36077
10°	32509
15°	26901
20°	20815
25°	15630
30°	11344
35°	7549
40°	4637
45°	2729
50°	1672
55°	1338
60°	1184
65°	986
70°	898
75°	847
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2729 cd/sqm



TEST NUMBER: P1271270
 CATALOG NUMBER: P3AS05R309827DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.1	13.8
10°-20°	32.6	29.9
20°-30°	29.7	27.2
30°-40°	17.9	16.5
40°-50°	7.2	6.6
50°-60°	3.2	2.9
60°-70°	1.9	1.8
70°-80°	1.0	1.0
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	77.4	71.0
0°-40°	95.3	87.5
0°-60°	105.7	97.0
0°-90°	109.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	109.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	170	
5°	164	15
15°	118	33
25°	65	30
35°	28	18
45°	9	7
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1271270
CATALOG NUMBER: P3AS05R309827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	169.9
1°	169.7
2°	169.0
3°	167.8
4°	166.1
5°	163.9
6°	161.2
7°	158.4
8°	154.7
9°	150.4
10°	146.0
11°	141.0
12°	135.6
13°	130.1
14°	124.2
15°	118.5
17.5°	103.4
20°	89.2
22.5°	76.1
25°	64.6
27.5°	54.1
30°	44.8
32.5°	36.2
35°	28.2
37.5°	21.6
40°	16.2
42.5°	11.8
45°	8.8
47.5°	6.6
50°	4.9
52.5°	3.9
55°	3.5
57.5°	3.0
60°	2.7
62.5°	2.2
65°	1.9
67.5°	1.7
70°	1.4
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.5
82.5°	0.3
85°	0.3
87.5°	0.2



TEST NUMBER: P1271270
CATALOG NUMBER: P3AS05R309827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)