

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272142

Luminaire Tested: P3AS13R659827DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272142
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659827DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 836.0 lumens
Efficiency: N/A
Efficacy: 57.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272142

CATALOG NUMBER: P3AS13R659827DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1272142

CATALOG NUMBER: P3AS13R659827DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		87
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	204304
5°	192273
10°	189843
15°	186494
20°	176065
25°	163413
30°	127032
35°	73482
40°	29598
45°	13614
50°	5322
55°	2064
60°	1798
65°	1764
70°	1731
75°	1694
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13614 cd/sqm

TEST NUMBER: P1272142

CATALOG NUMBER: P3AS13R659827DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	9.9
10°-20°	229.4	27.4
20°-30°	300.3	35.9
30°-40°	173.9	20.8
40°-50°	37.2	4.5
50°-60°	6.1	0.7
60°-70°	3.4	0.4
70°-80°	2.0	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.7	73.3
0°-40°	786.7	94.1
0°-60°	830.0	99.3
0°-90°	836.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	836.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	932	
5°	874	83
15°	822	229
25°	675	300
35°	274	174
45°	44	37
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1272142

CATALOG NUMBER: P3AS13R659827DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	931.7
2.5°	905.3
5°	873.5
7.5°	860.7
10°	852.6
12.5°	841.1
15°	821.5
17.5°	791.1
20°	754.5
22.5°	720.1
25°	675.4
27.5°	600.4
30°	501.7
32.5°	388.8
35°	274.5
37.5°	173.8
40°	103.4
42.5°	64.9
45°	43.9
47.5°	28.4
50°	15.6
52.5°	7.4
55°	5.4
57.5°	4.7
60°	4.1
62.5°	4.1
65°	3.4
67.5°	2.7
70°	2.7
72.5°	2.0
75°	2.0
77.5°	1.4
80°	1.4
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)