

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272187

Luminaire Tested: P3AS13R709827DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1272187  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R709827DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 98CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 486.0 lumens  
Efficiency: N/A  
Efficacy: 33.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272187  
CATALOG NUMBER: P3AS13R709827DE010 E3DLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1272187  
 CATALOG NUMBER: P3AS13R709827DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114004
5°	111908
10°	105520
15°	95755
20°	83774
25°	70649
30°	57857
35°	44892
40°	32117
45°	20343
50°	10132
55°	6193
60°	5350
65°	4929
70°	4360
75°	3982
80°	3410
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20343 cd/sqm



TEST NUMBER: P1272187  
 CATALOG NUMBER: P3AS13R709827DE010 E3DLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	9.8
10°-20°	117.4	24.1
20°-30°	133.7	27.5
30°-40°	104.5	21.5
40°-50°	51.4	10.6
50°-60°	15.8	3.2
60°-70°	9.4	1.9
70°-80°	5.0	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.5	61.4
0°-40°	403.0	82.9
0°-60°	470.2	96.7
0°-90°	486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	486.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	520	
5°	508	47
15°	422	117
25°	292	134
35°	168	105
45°	66	51
55°	16	16
65°	10	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1272187  
CATALOG NUMBER: P3AS13R709827DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	519.9
2.5°	517.2
5°	508.4
7.5°	494.2
10°	473.9
12.5°	450.2
15°	421.8
17.5°	391.4
20°	359.0
22.5°	325.2
25°	292.0
27.5°	259.6
30°	228.5
32.5°	197.4
35°	167.7
37.5°	139.3
40°	112.2
42.5°	87.2
45°	65.6
47.5°	46.0
50°	29.7
52.5°	19.6
55°	16.2
57.5°	14.2
60°	12.2
62.5°	10.8
65°	9.5
67.5°	8.1
70°	6.8
72.5°	5.4
75°	4.7
77.5°	4.1
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)