

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271335

Luminaire Tested: P3AS05R409827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 253.0 lumens
Efficiency: N/A
Efficacy: 35.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271335
CATALOG NUMBER: P3AS05R409827DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1271335
 CATALOG NUMBER: P3AS05R409827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80	80	80	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78788
5°	77173
10°	71853
15°	62634
20°	50474
25°	37841
30°	26612
35°	17427
40°	10563
45°	6295
50°	3753
55°	3020
60°	2719
65°	2335
70°	2180
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6295 cd/sqm



TEST NUMBER: P1271335
 CATALOG NUMBER: P3AS05R409827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.6	12.9
10°-20°	76.0	30.0
20°-30°	71.6	28.3
30°-40°	41.4	16.4
40°-50°	16.5	6.5
50°-60°	7.3	2.9
60°-70°	4.5	1.8
70°-80°	2.4	0.9
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	180.2	71.2
0°-40°	221.6	87.6
0°-60°	245.4	97.0
0°-90°	253.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	253.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	359	
5°	351	33
15°	276	76
25°	156	72
35°	65	41
45°	20	17
55°	8	7
65°	4	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1271335
CATALOG NUMBER: P3AS05R409827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	359.3
2.5°	357.2
5°	350.6
7.5°	338.6
10°	322.7
12.5°	301.4
15°	275.9
17.5°	247.3
20°	216.3
22.5°	185.3
25°	156.4
27.5°	129.5
30°	105.1
32.5°	83.7
35°	65.1
37.5°	49.3
40°	36.9
42.5°	27.6
45°	20.3
47.5°	14.8
50°	11.0
52.5°	9.0
55°	7.9
57.5°	7.2
60°	6.2
62.5°	5.2
65°	4.5
67.5°	3.8
70°	3.4
72.5°	2.8
75°	2.1
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)