

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271346

Luminaire Tested: P3AS05R459827DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459827DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 385.0 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271346

CATALOG NUMBER: P3AS05R459827DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1271346

CATALOG NUMBER: P3AS05R459827DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88		
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83		
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78		
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74		
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70		
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66		
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62		
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144572
5°	141184
10°	129791
15°	109967
20°	85337
25°	59641
30°	37575
35°	22111
40°	12509
45°	6078
50°	2115
55°	1720
60°	1667
65°	1608
70°	1539
75°	1440
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6078 cd/sqm

TEST NUMBER: P1271346

CATALOG NUMBER: P3AS05R459827DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.4	15.4
10°-20°	133.0	34.6
20°-30°	113.0	29.3
30°-40°	53.9	14.0
40°-50°	16.2	4.2
50°-60°	4.1	1.1
60°-70°	3.1	0.8
70°-80°	1.8	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	305.4	79.3
0°-40°	359.2	93.3
0°-60°	379.6	98.6
0°-90°	385.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	385.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	659	
5°	641	59
15°	484	133
25°	246	113
35°	83	54
45°	20	16
55°	4	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1271346

CATALOG NUMBER: P3AS05R459827DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	659.3
2.5°	655.2
5°	641.4
7.5°	617.7
10°	582.9
12.5°	536.8
15°	484.4
17.5°	426.2
20°	365.7
22.5°	304.0
25°	246.5
27.5°	194.2
30°	148.4
32.5°	111.6
35°	82.6
37.5°	60.9
40°	43.7
42.5°	30.3
45°	19.6
47.5°	11.0
50°	6.2
52.5°	4.8
55°	4.5
57.5°	4.1
60°	3.8
62.5°	3.4
65°	3.1
67.5°	2.8
70°	2.4
72.5°	2.1
75°	1.7
77.5°	1.4
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)