

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272189

Luminaire Tested: P3AS13R709827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 486.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272189

CATALOG NUMBER: P3AS13R709827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1272189

CATALOG NUMBER: P3AS13R709827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114004
5°	111908
10°	105520
15°	95755
20°	83774
25°	70649
30°	57857
35°	44892
40°	32117
45°	20343
50°	10132
55°	6193
60°	5350
65°	4929
70°	4360
75°	3982
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20343 cd/sqm

TEST NUMBER: P1272189

CATALOG NUMBER: P3AS13R709827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	9.8
10°-20°	117.4	24.1
20°-30°	133.7	27.5
30°-40°	104.5	21.5
40°-50°	51.4	10.6
50°-60°	15.8	3.2
60°-70°	9.4	1.9
70°-80°	5.0	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.5	61.4
0°-40°	403.0	82.9
0°-60°	470.2	96.7
0°-90°	486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	486.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	520	
5°	508	47
15°	422	117
25°	292	134
35°	168	105
45°	66	51
55°	16	16
65°	10	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1272189

CATALOG NUMBER: P3AS13R709827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	519.9
2.5°	517.2
5°	508.4
7.5°	494.2
10°	473.9
12.5°	450.2
15°	421.8
17.5°	391.4
20°	359.0
22.5°	325.2
25°	292.0
27.5°	259.6
30°	228.5
32.5°	197.4
35°	167.7
37.5°	139.3
40°	112.2
42.5°	87.2
45°	65.6
47.5°	46.0
50°	29.7
52.5°	19.6
55°	16.2
57.5°	14.2
60°	12.2
62.5°	10.8
65°	9.5
67.5°	8.1
70°	6.8
72.5°	5.4
75°	4.7
77.5°	4.1
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)