

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272208

Luminaire Tested: P3AS17R159827DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159827DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1136.0 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272208

CATALOG NUMBER: P3AS17R159827DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1272208

CATALOG NUMBER: P3AS17R159827DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	970449
5°	861411
10°	598208
15°	353782
20°	201478
25°	115168
30°	63731
35°	33970
40°	18807
45°	10172
50°	6345
55°	5008
60°	4298
65°	3995
70°	3526
75°	3728
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10172 cd/sqm

TEST NUMBER: P1272208

CATALOG NUMBER: P3AS17R159827DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.8	29.3
10°-20°	439.2	38.7
20°-30°	226.1	19.9
30°-40°	84.9	7.5
40°-50°	27.8	2.4
50°-60°	11.9	1.0
60°-70°	7.6	0.7
70°-80°	4.5	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	998.1	87.9
0°-40°	1083.0	95.3
0°-60°	1122.7	98.8
0°-90°	1136.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1136.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4426	
5°	3913	333
15°	1558	439
25°	476	226
35°	127	85
45°	33	28
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1272208

CATALOG NUMBER: P3AS17R159827DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4425.6
1°	4416.8
2°	4358.8
3°	4248.3
4°	4102.7
5°	3913.4
6°	3698.9
7°	3463.6
8°	3202.1
9°	2943.8
10°	2686.6
12.5°	2067.2
15°	1558.4
17.5°	1166.6
20°	863.4
22.5°	644.6
25°	476.0
27.5°	346.9
30°	251.7
32.5°	178.4
35°	126.9
37.5°	90.8
40°	65.7
42.5°	47.1
45°	32.8
47.5°	24.1
50°	18.6
52.5°	15.3
55°	13.1
57.5°	10.9
60°	9.8
62.5°	8.8
65°	7.7
67.5°	6.6
70°	5.5
72.5°	5.5
75°	4.4
77.5°	3.3
80°	2.2
82.5°	2.2
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)