

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271353

Luminaire Tested: P3AS05R459827DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459827DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 299.0 lumens
Efficiency: N/A
Efficacy: 41.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271353

CATALOG NUMBER: P3AS05R459827DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1271353

CATALOG NUMBER: P3AS05R459827DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63394
5°	62271
10°	58917
15°	53735
20°	47511
25°	41277
30°	35423
35°	29526
40°	21984
45°	13459
50°	6243
55°	4855
60°	4693
65°	4307
70°	3975
75°	3813
80°	3536
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13459 cd/sqm

TEST NUMBER: P1271353

CATALOG NUMBER: P3AS05R459827DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.4	8.8
10°-20°	65.9	22.0
20°-30°	78.3	26.2
30°-40°	68.0	22.8
40°-50°	34.1	11.4
50°-60°	11.8	4.0
60°-70°	8.3	2.8
70°-80°	4.6	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	170.6	57.1
0°-40°	238.7	79.8
0°-60°	284.6	95.2
0°-90°	299.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	299.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	289	
5°	283	26
15°	237	66
25°	171	78
35°	110	68
45°	43	34
55°	13	12
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1271353

CATALOG NUMBER: P3AS05R459827DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	289.1
2.5°	287.7
5°	282.9
7.5°	275.3
10°	264.6
12.5°	251.5
15°	236.7
17.5°	220.2
20°	203.6
22.5°	186.8
25°	170.6
27.5°	155.1
30°	139.9
32.5°	125.4
35°	110.3
37.5°	94.1
40°	76.8
42.5°	60.0
45°	43.4
47.5°	28.6
50°	18.3
52.5°	14.1
55°	12.7
57.5°	11.7
60°	10.7
62.5°	9.6
65°	8.3
67.5°	7.2
70°	6.2
72.5°	5.2
75°	4.5
77.5°	3.4
80°	2.8
82.5°	2.1
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)