

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272267

Luminaire Tested: P3AS17R259827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 431.0 lumens
Efficiency: N/A
Efficacy: 21.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272267

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272267

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102426
5°	99978
10°	92650
15°	82520
20°	70916
25°	60270
30°	49628
35°	38655
40°	27824
45°	17645
50°	10439
55°	7187
60°	6578
65°	6123
70°	5514
75°	4999
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17645 cd/sqm

TEST NUMBER: P1272267

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.1	9.8
10°-20°	100.9	23.4
20°-30°	114.0	26.5
30°-40°	90.2	20.9
40°-50°	45.5	10.6
50°-60°	18.2	4.2
60°-70°	11.7	2.7
70°-80°	6.4	1.5
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	257.0	59.6
0°-40°	347.2	80.6
0°-60°	411.0	95.4
0°-90°	431.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	431.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	467	
5°	454	42
15°	364	101
25°	249	114
35°	144	90
45°	57	46
55°	19	18
65°	12	12
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1272267

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	467.1
1°	467.1
2°	465.5
3°	462.8
4°	459.1
5°	454.2
6°	448.3
7°	441.4
8°	433.8
9°	425.3
10°	416.1
11°	405.9
12°	396.3
13°	385.0
14°	374.2
15°	363.5
17.5°	333.4
20°	303.9
22.5°	276.0
25°	249.1
27.5°	222.8
30°	196.0
32.5°	170.7
35°	144.4
37.5°	120.3
40°	97.2
42.5°	75.7
45°	56.9
47.5°	42.4
50°	30.6
52.5°	23.1
55°	18.8
57.5°	17.2
60°	15.0
62.5°	13.4
65°	11.8
67.5°	10.2
70°	8.6
72.5°	7.5
75°	5.9
77.5°	4.8
80°	3.8
82.5°	2.7
85°	1.6
87.5°	0.5



TEST NUMBER: P1272267

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)