

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271411

Luminaire Tested: P3AS05R559827DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559827DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 292.0 lumens
Efficiency: N/A
Efficacy: 40.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271411

CATALOG NUMBER: P3AS05R559827DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1271411

CATALOG NUMBER: P3AS05R559827DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54908
5°	54193
10°	52059
15°	48695
20°	44431
25°	39631
30°	34664
35°	28804
40°	22700
45°	15412
50°	9415
55°	4893
60°	4517
65°	4307
70°	3975
75°	3474
80°	3536
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15412 cd/sqm

TEST NUMBER: P1271411

CATALOG NUMBER: P3AS05R559827DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.1	7.9
10°-20°	60.0	20.5
20°-30°	75.1	25.7
30°-40°	67.0	23.0
40°-50°	39.2	13.4
50°-60°	13.6	4.6
60°-70°	8.2	2.8
70°-80°	4.5	1.6
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.1	54.2
0°-40°	225.1	77.1
0°-60°	277.9	95.2
0°-90°	292.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	292.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	250	
5°	246	23
15°	214	60
25°	164	75
35°	108	67
45°	50	39
55°	13	14
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1271411

CATALOG NUMBER: P3AS05R559827DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	250.4
2.5°	249.0
5°	246.2
7.5°	240.7
10°	233.8
12.5°	225.2
15°	214.5
17.5°	203.1
20°	190.4
22.5°	177.3
25°	163.8
27.5°	150.4
30°	136.9
32.5°	122.4
35°	107.6
37.5°	93.1
40°	79.3
42.5°	64.5
45°	49.7
47.5°	37.9
50°	27.6
52.5°	17.9
55°	12.8
57.5°	11.4
60°	10.3
62.5°	9.3
65°	8.3
67.5°	7.2
70°	6.2
72.5°	5.2
75°	4.1
77.5°	3.4
80°	2.8
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)