

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272269

Luminaire Tested: P3AS17R259827DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259827DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 879.0 lumens
Efficiency: N/A
Efficacy: 43.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272269

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1272269

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	105	102		103	101	99		99	98	96		96	94	93
2	106	100	96	92		104	99	94	91		95	92	89		92	89	87		89	87	85
3	100	92	87	82		98	91	86	82		88	84	80		86	82	79		83	80	78
4	94	85	79	74		92	84	78	74		82	77	73		80	76	72		78	74	71
5	89	79	73	68		87	78	72	68		76	71	67		75	70	66		73	69	66
6	84	74	67	62		82	73	67	62		71	66	62		70	65	61		69	64	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	54		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	61	54	50		70	60	54	50		59	54	50		58	53	50		57	53	49
10	68	57	51	47		67	57	51	47		56	50	47		55	50	46		54	50	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208909
5°	203918
10°	188974
15°	168287
20°	144633
25°	122935
30°	101205
35°	78862
40°	56735
45°	36004
50°	21287
55°	14642
60°	13464
65°	12505
70°	11220
75°	10167
80°	9723
85°	8303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 36004 cd/sqm

TEST NUMBER: P1272269

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.9	9.8
10°-20°	205.8	23.4
20°-30°	232.5	26.5
30°-40°	183.9	20.9
40°-50°	92.9	10.6
50°-60°	37.2	4.2
60°-70°	23.8	2.7
70°-80°	13.1	1.5
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.3	59.6
0°-40°	708.2	80.6
0°-60°	838.3	95.4
0°-90°	879.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	879.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	953	
5°	926	86
15°	741	206
25°	508	233
35°	295	184
45°	116	93
55°	38	37
65°	24	24
75°	12	13
85°	3	4
90°	0	

TEST NUMBER: P1272269

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	952.7
1°	952.7
2°	949.4
3°	943.9
4°	936.3
5°	926.4
6°	914.4
7°	900.1
8°	884.8
9°	867.3
10°	848.7
11°	827.9
12°	808.1
13°	785.2
14°	763.2
15°	741.3
17.5°	680.0
20°	619.8
22.5°	562.9
25°	508.1
27.5°	454.4
30°	399.7
32.5°	348.2
35°	294.6
37.5°	245.3
40°	198.2
42.5°	154.4
45°	116.1
47.5°	86.5
50°	62.4
52.5°	47.1
55°	38.3
57.5°	35.0
60°	30.7
62.5°	27.4
65°	24.1
67.5°	20.8
70°	17.5
72.5°	15.3
75°	12.0
77.5°	9.9
80°	7.7
82.5°	5.5
85°	3.3
87.5°	1.1



TEST NUMBER: P1272269

CATALOG NUMBER: P3AS17R259827DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)