

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272289

Luminaire Tested: P3AS17R309827DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272289
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309827DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1382.0 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272289
CATALOG NUMBER: P3AS17R309827DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1272289

CATALOG NUMBER: P3AS17R309827DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	97	96	95
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	95	93	92
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	93	91	89
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	90	88	86
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	88	85	83
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	86	83	81
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	84	81	79
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	82	79	77
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	80	77	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1099561
5°	1085227
10°	947500
15°	602251
20°	238604
25°	79698
30°	37094
35°	16811
40°	6441
45°	3163
50°	921
55°	421
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3163 cd/sqm



TEST NUMBER: P1272289

CATALOG NUMBER: P3AS17R309827DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	450.8	32.6
10°-20°	699.0	50.6
20°-30°	180.2	13.0
30°-40°	42.4	3.1
40°-50°	8.3	0.6
50°-60°	0.9	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1330.0	96.2
0°-40°	1372.3	99.3
0°-60°	1381.5	100.0
0°-90°	1382.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1382.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5014	
5°	4930	451
15°	2653	699
25°	329	180
35°	63	42
45°	10	8
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1272289

CATALOG NUMBER: P3AS17R309827DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5014.4
1°	5010.6
2°	4998.8
3°	4985.4
4°	4965.6
5°	4930.2
6°	4872.8
7°	4777.3
8°	4646.9
9°	4476.9
10°	4255.3
11°	3991.9
12°	3704.3
13°	3373.3
14°	3026.8
15°	2652.9
16°	2286.4
17°	1933.4
18°	1594.9
19°	1284.3
20°	1022.5
21°	804.7
22°	633.0
23°	501.1
24°	401.3
25°	329.4
26°	274.7
27°	233.4
28°	201.7
29°	172.7
30°	146.5
32.5°	92.3
35°	62.8
37.5°	39.2
40°	22.5
42.5°	15.0
45°	10.2
47.5°	5.9
50°	2.7
52.5°	1.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P1272289
CATALOG NUMBER: P3AS17R309827DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)