

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271447

Luminaire Tested: P3AS05R609827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 251.0 lumens
Efficiency: N/A
Efficacy: 34.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271447

CATALOG NUMBER: P3AS05R609827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271447

CATALOG NUMBER: P3AS05R609827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63613
5°	62183
10°	58226
15°	52236
20°	44921
25°	37139
30°	29346
35°	21790
40°	15000
45°	9427
50°	5185
55°	3020
60°	2719
65°	2335
70°	1988
75°	2033
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9427 cd/sqm

TEST NUMBER: P1271447

CATALOG NUMBER: P3AS05R609827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.3	10.5
10°-20°	63.9	25.5
20°-30°	70.1	27.9
30°-40°	51.1	20.3
40°-50°	24.1	9.6
50°-60°	7.9	3.1
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	160.3	63.9
0°-40°	211.3	84.2
0°-60°	243.4	97.0
0°-90°	251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	251.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	290	
5°	282	26
15°	230	64
25°	154	70
35°	81	51
45°	30	24
55°	8	8
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1271447

CATALOG NUMBER: P3AS05R609827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	290.1
2.5°	288.4
5°	282.5
7.5°	273.5
10°	261.5
12.5°	247.0
15°	230.1
17.5°	211.8
20°	192.5
22.5°	172.8
25°	153.5
27.5°	134.2
30°	115.9
32.5°	98.3
35°	81.4
37.5°	66.2
40°	52.4
42.5°	40.4
45°	30.4
47.5°	22.1
50°	15.2
52.5°	10.0
55°	7.9
57.5°	6.9
60°	6.2
62.5°	5.2
65°	4.5
67.5°	3.8
70°	3.1
72.5°	2.8
75°	2.4
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)