

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272322

Luminaire Tested: P3AS17R359827DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1272322  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R359827DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1150.0 lumens  
Efficiency: N/A  
Efficacy: 56.4 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272322  
CATALOG NUMBER: P3AS17R359827DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1272322  
 CATALOG NUMBER: P3AS17R359827DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	580019
5°	557428
10°	485673
15°	372011
20°	248895
25°	150589
30°	86418
35°	48318
40°	25677
45°	13242
50°	6345
55°	5008
60°	4780
65°	3995
70°	4231
75°	3728
80°	4167
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13242 cd/sqm



TEST NUMBER: P1272322  
 CATALOG NUMBER: P3AS17R359827DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	230.4	20.0
10°-20°	446.5	38.8
20°-30°	292.3	25.4
30°-40°	118.6	10.3
40°-50°	35.6	3.1
50°-60°	12.1	1.0
60°-70°	8.1	0.7
70°-80°	4.8	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.2	84.3
0°-40°	1087.8	94.6
0°-60°	1135.5	98.7
0°-90°	1150.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1150.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2645	
5°	2532	230
15°	1639	447
25°	622	292
35°	180	119
45°	43	36
55°	13	12
65°	8	8
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1272322  
CATALOG NUMBER: P3AS17R359827DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2645.1
1°	2640.7
2°	2628.6
3°	2604.6
4°	2576.1
5°	2532.4
6°	2477.7
7°	2416.4
8°	2347.5
9°	2268.8
10°	2181.2
11°	2083.9
12°	1982.2
13°	1868.4
14°	1760.1
15°	1638.7
17.5°	1344.4
20°	1066.6
22.5°	820.4
25°	622.4
27.5°	463.8
30°	341.3
32.5°	250.5
35°	180.5
37.5°	128.0
40°	89.7
42.5°	62.4
45°	42.7
47.5°	28.4
50°	18.6
52.5°	14.2
55°	13.1
57.5°	12.0
60°	10.9
62.5°	9.8
65°	7.7
67.5°	6.6
70°	6.6
72.5°	5.5
75°	4.4
77.5°	3.3
80°	3.3
82.5°	2.2
85°	1.1
87.5°	1.1



TEST NUMBER: P1272322  
CATALOG NUMBER: P3AS17R359827DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)