

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271451

Luminaire Tested: P3AS05R659827DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659827DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 426.0 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271451

CATALOG NUMBER: P3AS05R659827DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1271451

CATALOG NUMBER: P3AS05R659827DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104114
5°	97975
10°	96725
15°	95029
20°	89724
25°	83279
30°	64719
35°	37450
40°	15085
45°	6946
50°	2695
55°	1070
60°	921
65°	882
70°	898
75°	847
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6946 cd/sqm

TEST NUMBER: P1271451

CATALOG NUMBER: P3AS05R659827DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.3	9.9
10°-20°	116.9	27.4
20°-30°	153.0	35.9
30°-40°	88.6	20.8
40°-50°	19.0	4.5
50°-60°	3.1	0.7
60°-70°	1.7	0.4
70°-80°	1.0	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	312.2	73.3
0°-40°	400.8	94.1
0°-60°	422.9	99.3
0°-90°	426.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	426.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	475	
5°	445	42
15°	419	117
25°	344	153
35°	140	89
45°	22	19
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271451

CATALOG NUMBER: P3AS05R659827DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	474.8
2.5°	461.3
5°	445.1
7.5°	438.6
10°	434.4
12.5°	428.6
15°	418.6
17.5°	403.1
20°	384.5
22.5°	366.9
25°	344.2
27.5°	305.9
30°	255.6
32.5°	198.1
35°	139.9
37.5°	88.5
40°	52.7
42.5°	33.1
45°	22.4
47.5°	14.5
50°	7.9
52.5°	3.8
55°	2.8
57.5°	2.4
60°	2.1
62.5°	2.1
65°	1.7
67.5°	1.4
70°	1.4
72.5°	1.0
75°	1.0
77.5°	0.7
80°	0.7
82.5°	0.3
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)