

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271459

Luminaire Tested: P3AS05R659827DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271459
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659827DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 169.0 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271459

CATALOG NUMBER: P3AS05R659827DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271459

CATALOG NUMBER: P3AS05R659827DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39865
5°	39379
10°	37875
15°	35483
20°	31923
25°	27098
30°	21193
35°	15098
40°	9876
45°	6109
50°	3104
55°	1109
60°	965
65°	986
70°	833
75°	847
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6109 cd/sqm

TEST NUMBER: P1271459

CATALOG NUMBER: P3AS05R659827DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.8	9.9
10°-20°	43.5	25.7
20°-30°	50.8	30.1
30°-40°	35.5	21.0
40°-50°	15.6	9.3
50°-60°	3.5	2.1
60°-70°	1.8	1.0
70°-80°	1.1	0.6
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	111.1	65.8
0°-40°	146.7	86.8
0°-60°	165.8	98.1
0°-90°	169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	169.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	182	
5°	179	17
15°	156	44
25°	112	51
35°	56	36
45°	20	16
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1271459

CATALOG NUMBER: P3AS05R659827DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	181.8
2.5°	181.1
5°	178.9
7.5°	175.2
10°	170.1
12.5°	163.9
15°	156.3
17.5°	147.1
20°	136.8
22.5°	125.2
25°	112.0
27.5°	98.2
30°	83.7
32.5°	69.7
35°	56.4
37.5°	44.8
40°	34.5
42.5°	26.1
45°	19.7
47.5°	14.5
50°	9.1
52.5°	4.7
55°	2.9
57.5°	2.5
60°	2.2
62.5°	2.0
65°	1.9
67.5°	1.5
70°	1.3
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)