

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271470

Luminaire Tested: P3AS05R659827DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659827DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 272.0 lumens
Efficiency: N/A
Efficacy: 37.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271470

CATALOG NUMBER: P3AS05R659827DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271470

CATALOG NUMBER: P3AS05R659827DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48395
5°	47744
10°	46158
15°	43519
20°	40137
25°	36438
30°	32283
35°	27465
40°	21841
45°	15412
50°	8972
55°	4893
60°	4561
65°	4099
70°	3783
75°	3474
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15412 cd/sqm

TEST NUMBER: P1271470

CATALOG NUMBER: P3AS05R659827DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.4	7.5
10°-20°	53.6	19.7
20°-30°	68.9	25.3
30°-40°	63.8	23.4
40°-50°	38.5	14.2
50°-60°	13.1	4.8
60°-70°	7.9	2.9
70°-80°	4.5	1.6
80°-90°	1.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	143.0	52.6
0°-40°	206.7	76.0
0°-60°	258.4	95.0
0°-90°	272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	221	
5°	217	20
15°	192	54
25°	151	69
35°	103	64
45°	50	39
55°	13	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1271470

CATALOG NUMBER: P3AS05R659827DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	220.7
2.5°	219.7
5°	216.9
7.5°	212.8
10°	207.3
12.5°	200.4
15°	191.7
17.5°	182.4
20°	172.0
22.5°	161.3
25°	150.6
27.5°	139.2
30°	127.5
32.5°	115.7
35°	102.6
37.5°	89.8
40°	76.3
42.5°	62.9
45°	49.7
47.5°	37.7
50°	26.3
52.5°	16.6
55°	12.8
57.5°	11.4
60°	10.4
62.5°	9.0
65°	7.9
67.5°	6.9
70°	5.9
72.5°	5.2
75°	4.1
77.5°	3.5
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)