

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272361

Luminaire Tested: P3AS17R409827DE010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1272361  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R409827DE010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 978.0 lumens  
Efficiency: N/A  
Efficacy: 47.9 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272361  
CATALOG NUMBER: P3AS17R409827DE010 E3DLD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1272361  
 CATALOG NUMBER: P3AS17R409827DE010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	219544
5°	215562
10°	203203
15°	184564
20°	162134
25°	138468
30°	114701
35°	88446
40°	62947
45°	42423
50°	23129
55°	16324
60°	15350
65°	14217
70°	12630
75°	12031
80°	9723
85°	8303

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 42423 cd/sqm



TEST NUMBER: P1272361  
 CATALOG NUMBER: P3AS17R409827DE010 E3DLD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.3	9.3
10°-20°	226.5	23.2
20°-30°	261.8	26.8
30°-40°	206.3	21.1
40°-50°	105.9	10.8
50°-60°	40.5	4.1
60°-70°	26.8	2.7
70°-80°	14.6	1.5
80°-90°	4.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	579.6	59.3
0°-40°	785.9	80.4
0°-60°	932.3	95.3
0°-90°	978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	978.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1001	
5°	979	91
15°	813	226
25°	572	262
35°	330	206
45°	137	106
55°	43	40
65°	27	27
75°	14	15
85°	3	4
90°	0	



TEST NUMBER: P1272361  
CATALOG NUMBER: P3AS17R409827DE010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1001.2
2.5°	995.7
5°	979.3
7.5°	950.9
10°	912.6
12.5°	867.7
15°	813.0
17.5°	756.1
20°	694.8
22.5°	632.4
25°	572.3
27.5°	512.1
30°	453.0
32.5°	392.8
35°	330.4
37.5°	272.5
40°	219.9
42.5°	175.1
45°	136.8
47.5°	99.6
50°	67.8
52.5°	49.2
55°	42.7
57.5°	38.3
60°	35.0
62.5°	30.6
65°	27.4
67.5°	23.0
70°	19.7
72.5°	16.4
75°	14.2
77.5°	10.9
80°	7.7
82.5°	6.6
85°	3.3
87.5°	2.2
90°	0.0

(END OF REPORT)