

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272384

Luminaire Tested: P3AS17R459827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 465.0 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272384

CATALOG NUMBER: P3AS17R459827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272384

CATALOG NUMBER: P3AS17R459827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98589
5°	96852
10°	91648
15°	83587
20°	73903
25°	64189
30°	55097
35°	45909
40°	34207
45°	20932
50°	9688
55°	7570
60°	7280
65°	6693
70°	6155
75°	5931
80°	5430
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20932 cd/sqm

TEST NUMBER: P1272384

CATALOG NUMBER: P3AS17R459827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.1	8.8
10°-20°	102.5	22.0
20°-30°	121.8	26.2
30°-40°	105.8	22.8
40°-50°	53.1	11.4
50°-60°	18.4	4.0
60°-70°	12.9	2.8
70°-80°	7.2	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	265.4	57.1
0°-40°	371.2	79.8
0°-60°	442.7	95.2
0°-90°	465.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	465.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	450	
5°	440	41
15°	368	103
25°	265	122
35°	172	106
45°	68	53
55°	20	18
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1272384

CATALOG NUMBER: P3AS17R459827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	449.6
2.5°	447.5
5°	440.0
7.5°	428.2
10°	411.6
12.5°	391.2
15°	368.2
17.5°	342.4
20°	316.7
22.5°	290.5
25°	265.3
27.5°	241.1
30°	217.6
32.5°	195.1
35°	171.5
37.5°	146.3
40°	119.5
42.5°	93.2
45°	67.5
47.5°	44.5
50°	28.4
52.5°	22.0
55°	19.8
57.5°	18.2
60°	16.6
62.5°	15.0
65°	12.9
67.5°	11.3
70°	9.6
72.5°	8.0
75°	7.0
77.5°	5.4
80°	4.3
82.5°	3.2
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)