

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272390

Luminaire Tested: P3AS17R459827DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459827DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 387.0 lumens
Efficiency: N/A
Efficacy: 19.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272390
CATALOG NUMBER: P3AS17R459827DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1272390
 CATALOG NUMBER: P3AS17R459827DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115276
5°	112635
10°	103917
15°	90352
20°	74230
25°	57753
30°	42639
35°	30008
40°	18721
45°	10141
50°	5492
55°	4702
60°	4254
65°	3632
70°	3077
75°	3219
80°	2652
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10141 cd/sqm



TEST NUMBER: P1272390
 CATALOG NUMBER: P3AS17R459827DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	12.2
10°-20°	110.0	28.4
20°-30°	109.2	28.2
30°-40°	70.3	18.2
40°-50°	27.1	7.0
50°-60°	11.0	2.8
60°-70°	7.0	1.8
70°-80°	3.8	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	266.6	68.9
0°-40°	337.0	87.1
0°-60°	375.1	96.9
0°-90°	387.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	387.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	526	
5°	512	47
15°	398	110
25°	239	109
35°	112	70
45°	33	27
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1272390
CATALOG NUMBER: P3AS17R459827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	525.7
2.5°	523.0
5°	511.7
7.5°	492.4
10°	466.7
12.5°	434.5
15°	398.0
17.5°	358.3
20°	318.1
22.5°	277.3
25°	238.7
27.5°	202.2
30°	168.4
32.5°	138.9
35°	112.1
37.5°	88.0
40°	65.4
42.5°	47.2
45°	32.7
47.5°	22.0
50°	16.1
52.5°	13.4
55°	12.3
57.5°	10.7
60°	9.7
62.5°	8.0
65°	7.0
67.5°	5.9
70°	4.8
72.5°	4.3
75°	3.8
77.5°	2.7
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)