

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271533

Luminaire Tested: P3AS09R159827DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159827DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 98CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 237.0 lumens
Efficiency: N/A
Efficacy: 21.5 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271533

CATALOG NUMBER: P3AS09R159827DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1271533

CATALOG NUMBER: P3AS09R159827DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	92	92	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	83	83	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	76	76	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	70	70	68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	65	65	63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	60	60	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	57	57	55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	53	53	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	50	50	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	48	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88699
5°	81444
10°	64906
15°	48491
20°	36823
25°	27897
30°	20636
35°	14750
40°	10076
45°	7071
50°	6004
55°	5887
60°	6096
65°	6486
70°	6604
75°	6863
80°	7450
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 82.5°
Luminance: 8568 cd/sqm

TEST NUMBER: P1271533

CATALOG NUMBER: P3AS09R159827DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.8	13.8
10°-20°	59.9	25.3
20°-30°	53.1	22.4
30°-40°	34.8	14.7
40°-50°	18.6	7.8
50°-60°	14.0	5.9
60°-70°	12.1	5.1
70°-80°	8.3	3.5
80°-90°	3.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	145.8	61.5
0°-40°	180.6	76.2
0°-60°	213.2	90.0
0°-90°	237.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	237.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	404	
5°	370	33
15°	214	60
25°	115	53
35°	55	35
45°	23	19
55°	15	14
65°	12	12
75°	8	8
85°	3	3
90°	0	

TEST NUMBER: P1271533

CATALOG NUMBER: P3AS09R159827DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	404.5
2.5°	395.0
5°	370.0
7.5°	333.3
10°	291.5
12.5°	251.1
15°	213.6
17.5°	183.5
20°	157.8
22.5°	135.1
25°	115.3
27.5°	97.6
30°	81.5
32.5°	67.5
35°	55.1
37.5°	44.1
40°	35.2
42.5°	27.9
45°	22.8
47.5°	19.8
50°	17.6
52.5°	16.9
55°	15.4
57.5°	14.7
60°	13.9
62.5°	13.2
65°	12.5
67.5°	11.0
70°	10.3
72.5°	8.8
75°	8.1
77.5°	6.6
80°	5.9
82.5°	5.1
85°	2.9
87.5°	1.5
90°	0.0

(END OF REPORT)