

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272451

Luminaire Tested: P3AS17R559827DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559827DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 796.0 lumens
Efficiency: N/A
Efficacy: 39.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272451
CATALOG NUMBER: P3AS17R559827DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1272451
 CATALOG NUMBER: P3AS17R559827DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216540
5°	211115
10°	196256
15°	174780
20°	148530
25°	119862
30°	91381
35°	64996
40°	42880
45°	25429
50°	14908
55°	9214
60°	8157
65°	7368
70°	6283
75°	5592
80°	5556
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25429 cd/sqm



TEST NUMBER: P1272451
 CATALOG NUMBER: P3AS17R559827DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.1	11.2
10°-20°	213.4	26.8
20°-30°	226.1	28.4
30°-40°	152.8	19.2
40°-50°	66.9	8.4
50°-60°	24.0	3.0
60°-70°	14.0	1.8
70°-80°	7.4	0.9
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	528.6	66.4
0°-40°	681.3	85.6
0°-60°	772.2	97.0
0°-90°	796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	988	
5°	959	89
15°	770	213
25°	495	226
35°	243	153
45°	82	67
55°	24	24
65°	14	14
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1272451
CATALOG NUMBER: P3AS17R559827DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	987.5
2.5°	979.8
5°	959.1
7.5°	925.2
10°	881.4
12.5°	828.9
15°	769.9
17.5°	704.3
20°	636.5
22.5°	565.4
25°	495.4
27.5°	426.5
30°	360.9
32.5°	298.5
35°	242.8
37.5°	192.5
40°	149.8
42.5°	112.6
45°	82.0
47.5°	60.1
50°	43.7
52.5°	30.6
55°	24.1
57.5°	21.9
60°	18.6
62.5°	16.4
65°	14.2
67.5°	12.0
70°	9.8
72.5°	8.7
75°	6.6
77.5°	5.5
80°	4.4
82.5°	3.3
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)