

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271558

Luminaire Tested: P3AS09R209827DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209827DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 350.0 lumens
Efficiency: N/A
Efficacy: 31.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271558
CATALOG NUMBER: P3AS09R209827DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1271558
 CATALOG NUMBER: P3AS09R209827DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	85	82	80	80	80	80
3	98	90	83	78	95	88	82	78	85	81	77	83	79	75	80	77	74	72	72	72	72
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66	66	66	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60	60	60	60
6	81	70	63	58	79	70	63	58	68	62	58	66	61	57	65	60	57	55	55	55	55
7	76	66	59	54	75	65	58	53	64	58	53	62	57	53	61	56	53	51	51	51	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47	47	47	47
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99268
5°	92208
10°	78088
15°	61113
20°	48118
25°	38349
30°	30840
35°	25136
40°	20782
45°	17521
50°	15010
55°	12884
60°	11271
65°	9910
70°	8463
75°	7456
80°	5556
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17521 cd/sqm



TEST NUMBER: P1271558
 CATALOG NUMBER: P3AS09R209827DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.8	10.8
10°-20°	75.4	21.5
20°-30°	73.2	20.9
30°-40°	59.1	16.9
40°-50°	43.9	12.6
50°-60°	30.5	8.7
60°-70°	19.1	5.5
70°-80°	9.3	2.7
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.4	53.3
0°-40°	245.5	70.2
0°-60°	320.0	91.4
0°-90°	350.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	350.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	453	
5°	419	38
15°	269	75
25°	158	73
35°	94	59
45°	56	44
55°	34	31
65°	19	19
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P1271558
CATALOG NUMBER: P3AS09R209827DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	452.7
2.5°	442.4
5°	418.9
7.5°	387.4
10°	350.7
12.5°	310.3
15°	269.2
17.5°	235.5
20°	206.2
22.5°	180.5
25°	158.5
27.5°	139.4
30°	121.8
32.5°	107.1
35°	93.9
37.5°	82.2
40°	72.6
42.5°	63.8
45°	56.5
47.5°	49.9
50°	44.0
52.5°	38.9
55°	33.7
57.5°	29.3
60°	25.7
62.5°	22.7
65°	19.1
67.5°	16.1
70°	13.2
72.5°	11.0
75°	8.8
77.5°	6.6
80°	4.4
82.5°	2.2
85°	1.5
87.5°	0.0
90°	0.0

(END OF REPORT)