

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271576

Luminaire Tested: P3AS09R259827DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1271576  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R259827DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 533.0 lumens  
Efficiency: N/A  
Efficacy: 48.5 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271576  
CATALOG NUMBER: P3AS09R259827DE010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1271576  
 CATALOG NUMBER: P3AS09R259827DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	341902
5°	318995
10°	255529
15°	173463
20°	104962
25°	61383
30°	34942
35°	19220
40°	10219
45°	5365
50°	3138
55°	2332
60°	2017
65°	2127
70°	1988
75°	1694
80°	1263
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5365 cd/sqm



TEST NUMBER: P1271576  
 CATALOG NUMBER: P3AS09R259827DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.6	24.1
10°-20°	210.1	39.4
20°-30°	120.0	22.5
30°-40°	47.4	8.9
40°-50°	14.5	2.7
50°-60°	5.7	1.1
60°-70°	3.9	0.7
70°-80°	2.1	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.7	86.1
0°-40°	506.1	94.9
0°-60°	526.3	98.7
0°-90°	533.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1559	
5°	1449	129
15°	764	210
25°	254	120
35°	72	47
45°	17	15
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1271576  
CATALOG NUMBER: P3AS09R259827DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1559.2
1°	1556.1
2°	1543.4
3°	1521.0
4°	1489.9
5°	1449.2
6°	1401.3
7°	1347.3
8°	1284.6
9°	1220.5
10°	1147.6
11°	1075.8
12°	996.8
13°	918.9
14°	838.9
15°	764.1
17.5°	592.4
20°	449.8
22.5°	337.7
25°	253.7
27.5°	188.0
30°	138.0
32.5°	99.8
35°	71.8
37.5°	50.9
40°	35.7
42.5°	24.4
45°	17.3
47.5°	12.2
50°	9.2
52.5°	7.1
55°	6.1
57.5°	5.6
60°	4.6
62.5°	4.1
65°	4.1
67.5°	3.6
70°	3.1
72.5°	2.5
75°	2.0
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5



TEST NUMBER: P1271576  
CATALOG NUMBER: P3AS09R259827DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)