

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272483

Luminaire Tested: P3AS17R659827DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659827DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1354.0 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272483

CATALOG NUMBER: P3AS17R659827DE010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1272483

CATALOG NUMBER: P3AS17R659827DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	330895
5°	311423
10°	307454
15°	302045
20°	285181
25°	264669
30°	205728
35°	119016
40°	47947
45°	22080
50°	8597
55°	3364
60°	2895
65°	2854
70°	2821
75°	2796
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22080 cd/sqm

TEST NUMBER: P1272483

CATALOG NUMBER: P3AS17R659827DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.5	9.9
10°-20°	371.5	27.4
20°-30°	486.4	35.9
30°-40°	281.7	20.8
40°-50°	60.3	4.5
50°-60°	9.8	0.7
60°-70°	5.4	0.4
70°-80°	3.2	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	992.4	73.3
0°-40°	1274.1	94.1
0°-60°	1344.2	99.3
0°-90°	1354.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1354.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1509	
5°	1415	134
15°	1330	372
25°	1094	486
35°	445	282
45°	71	60
55°	9	10
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1272483

CATALOG NUMBER: P3AS17R659827DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1509.0
2.5°	1466.3
5°	1414.8
7.5°	1394.0
10°	1380.8
12.5°	1362.2
15°	1330.5
17.5°	1281.2
20°	1222.1
22.5°	1166.2
25°	1093.9
27.5°	972.4
30°	812.5
32.5°	629.6
35°	444.6
37.5°	281.4
40°	167.5
42.5°	105.1
45°	71.2
47.5°	46.0
50°	25.2
52.5°	12.0
55°	8.8
57.5°	7.7
60°	6.6
62.5°	6.6
65°	5.5
67.5°	4.4
70°	4.4
72.5°	3.3
75°	3.3
77.5°	2.2
80°	2.2
82.5°	1.1
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)