

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271603

Luminaire Tested: P3AS09R309827DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309827DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 263.9 lumens
Efficiency: N/A
Efficacy: 24.0 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271603
CATALOG NUMBER: P3AS09R309827DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1271603

CATALOG NUMBER: P3AS09R309827DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154045
5°	146621
10°	123333
15°	88945
20°	55165
25°	31381
30°	17420
35°	9476
40°	5009
45°	2698
50°	1433
55°	956
60°	877
65°	882
70°	769
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2698 cd/sqm



TEST NUMBER: P1271603
 CATALOG NUMBER: P3AS09R309827DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	22.7
10°-20°	106.6	40.4
20°-30°	61.6	23.3
30°-40°	23.4	8.9
40°-50°	7.2	2.7
50°-60°	2.4	0.9
60°-70°	1.6	0.6
70°-80°	0.9	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.2	86.5
0°-40°	251.6	95.3
0°-60°	261.2	99.0
0°-90°	263.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	263.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	702	
5°	666	60
15°	392	107
25°	130	62
35°	35	23
45°	9	7
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1271603
CATALOG NUMBER: P3AS09R309827DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	702.5
1°	702.0
2°	697.8
3°	689.8
4°	679.8
5°	666.1
6°	648.7
7°	629.2
8°	607.5
9°	581.6
10°	553.9
11°	524.0
12°	492.3
13°	459.1
14°	425.5
15°	391.8
17.5°	309.0
20°	236.4
22.5°	175.3
25°	129.7
27.5°	94.3
30°	68.8
32.5°	49.6
35°	35.4
37.5°	24.7
40°	17.5
42.5°	12.2
45°	8.7
47.5°	6.0
50°	4.2
52.5°	3.0
55°	2.5
57.5°	2.2
60°	2.0
62.5°	1.7
65°	1.7
67.5°	1.5
70°	1.2
72.5°	1.0
75°	0.7
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0



TEST NUMBER: P1271603
CATALOG NUMBER: P3AS09R309827DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)