

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272580

Luminaire Tested: P3AS20R209827D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209827D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 722.1 lumens
Efficiency: N/A
Efficacy: 26.4 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272580

CATALOG NUMBER: P3AS20R209827D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272580

CATALOG NUMBER: P3AS20R209827D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	555504
5°	504951
10°	373206
15°	230853
20°	131845
25°	75270
30°	42209
35°	22968
40°	12566
45°	6915
50°	4060
55°	2944
60°	2763
65°	2542
70°	2244
75°	2372
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6915 cd/sqm

TEST NUMBER: P1272580

CATALOG NUMBER: P3AS20R209827D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.7	27.5
10°-20°	283.6	39.3
20°-30°	148.0	20.5
30°-40°	57.2	7.9
40°-50°	18.6	2.6
50°-60°	7.3	1.0
60°-70°	4.8	0.7
70°-80°	2.9	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	630.3	87.3
0°-40°	687.5	95.2
0°-60°	713.4	98.8
0°-90°	722.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	722.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2533	
5°	2294	199
15°	1017	284
25°	311	148
35°	86	57
45°	22	19
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1272580

CATALOG NUMBER: P3AS20R209827D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2533.3
1°	2528.4
2°	2498.4
3°	2452.4
4°	2381.2
5°	2294.0
6°	2190.8
7°	2076.4
8°	1943.9
9°	1814.9
10°	1676.1
12.5°	1332.2
15°	1016.9
17.5°	761.0
20°	565.0
22.5°	418.5
25°	311.1
27.5°	229.5
30°	166.7
32.5°	120.7
35°	85.8
37.5°	62.1
40°	43.9
42.5°	31.4
45°	22.3
47.5°	16.0
50°	11.9
52.5°	9.1
55°	7.7
57.5°	7.0
60°	6.3
62.5°	5.6
65°	4.9
67.5°	4.2
70°	3.5
72.5°	3.5
75°	2.8
77.5°	2.1
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)