

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271704

Luminaire Tested: P3AS09R459827DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459827DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 569.0 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271704

CATALOG NUMBER: P3AS09R459827DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1271704

CATALOG NUMBER: P3AS09R459827DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	213689
5°	208672
10°	191825
15°	162544
20°	126104
25°	88142
30°	55528
35°	32685
40°	18492
45°	8993
50°	3138
55°	2523
60°	2456
65°	2387
70°	2308
75°	2118
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8993 cd/sqm

TEST NUMBER: P1271704

CATALOG NUMBER: P3AS09R459827DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.8	15.4
10°-20°	196.6	34.6
20°-30°	166.9	29.3
30°-40°	79.6	14.0
40°-50°	24.0	4.2
50°-60°	6.1	1.1
60°-70°	4.6	0.8
70°-80°	2.7	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.3	79.3
0°-40°	531.0	93.3
0°-60°	561.0	98.6
0°-90°	569.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	569.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	974	
5°	948	88
15°	716	197
25°	364	167
35°	122	80
45°	29	24
55°	7	6
65°	5	5
75°	2	3
85°	0	1
90°	0	

TEST NUMBER: P1271704

CATALOG NUMBER: P3AS09R459827DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	974.5
2.5°	968.3
5°	948.0
7.5°	912.9
10°	861.5
12.5°	793.3
15°	716.0
17.5°	630.0
20°	540.4
22.5°	449.3
25°	364.3
27.5°	287.0
30°	219.3
32.5°	164.9
35°	122.1
37.5°	90.1
40°	64.6
42.5°	44.8
45°	29.0
47.5°	16.3
50°	9.2
52.5°	7.1
55°	6.6
57.5°	6.1
60°	5.6
62.5°	5.1
65°	4.6
67.5°	4.1
70°	3.6
72.5°	3.1
75°	2.5
77.5°	2.0
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)