

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272586

Luminaire Tested: P3AS20R209827D010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1272586  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R209827D010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1120.0 lumens  
Efficiency: N/A  
Efficacy: 40.9 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272586  
CATALOG NUMBER: P3AS20R209827D010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1272586  
 CATALOG NUMBER: P3AS20R209827D010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	277039
5°	269645
10°	248047
15°	218344
20°	187243
25°	157316
30°	127159
35°	96744
40°	68815
45°	45431
50°	28144
55°	18504
60°	16841
65°	15514
70°	14618
75°	13217
80°	12628
85°	10819

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 45431 cd/sqm



TEST NUMBER: P1272586  
 CATALOG NUMBER: P3AS20R209827D010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.3	10.1
10°-20°	267.8	23.9
20°-30°	297.2	26.5
30°-40°	226.7	20.2
40°-50°	116.1	10.4
50°-60°	47.7	4.3
60°-70°	29.7	2.7
70°-80°	16.7	1.5
80°-90°	4.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.3	60.6
0°-40°	905.0	80.8
0°-60°	1068.7	95.4
0°-90°	1120.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1120.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1263	
5°	1225	113
15°	962	268
25°	650	297
35°	361	227
45°	146	116
55°	48	48
65°	30	30
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P1272586  
CATALOG NUMBER: P3AS20R209827D010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1263.4
1°	1264.8
2°	1259.1
3°	1252.0
4°	1240.6
5°	1225.0
6°	1206.5
7°	1186.5
8°	1165.2
9°	1139.6
10°	1114.0
12.5°	1040.0
15°	961.8
17.5°	882.1
20°	802.4
22.5°	722.7
25°	650.2
27.5°	577.6
30°	502.2
32.5°	431.1
35°	361.4
37.5°	300.2
40°	240.4
42.5°	189.2
45°	146.5
47.5°	111.0
50°	82.5
52.5°	61.2
55°	48.4
57.5°	44.1
60°	38.4
62.5°	34.1
65°	29.9
67.5°	25.6
70°	22.8
72.5°	18.5
75°	15.6
77.5°	12.8
80°	10.0
82.5°	7.1
85°	4.3
87.5°	1.4
90°	0.0

(END OF REPORT)