

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271723

Luminaire Tested: P3AS09R509827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271723
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 219.0 lumens
Efficiency: N/A
Efficacy: 19.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271723

CATALOG NUMBER: P3AS09R509827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271723

CATALOG NUMBER: P3AS09R509827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44514
5°	43848
10°	41905
15°	38820
20°	34886
25°	30655
30°	26080
35°	21148
40°	15887
45°	10234
50°	4844
55°	3823
60°	3596
65°	3373
70°	3013
75°	2711
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10234 cd/sqm

TEST NUMBER: P1271723

CATALOG NUMBER: P3AS09R509827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.7	8.5
10°-20°	47.7	21.8
20°-30°	57.9	26.5
30°-40°	49.1	22.4
40°-50°	25.5	11.6
50°-60°	9.2	4.2
60°-70°	6.3	2.9
70°-80°	3.4	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	124.3	56.8
0°-40°	173.4	79.2
0°-60°	208.1	95.0
0°-90°	219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	219.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	203	
5°	199	19
15°	171	48
25°	127	58
35°	79	49
45°	33	26
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1271723

CATALOG NUMBER: P3AS09R509827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	203.0
2.5°	202.2
5°	199.2
7.5°	194.7
10°	188.2
12.5°	180.0
15°	171.0
17.5°	160.7
20°	149.5
22.5°	138.0
25°	126.7
27.5°	115.0
30°	103.0
32.5°	91.0
35°	79.0
37.5°	67.2
40°	55.5
42.5°	44.2
45°	33.0
47.5°	22.0
50°	14.2
52.5°	11.0
55°	10.0
57.5°	9.0
60°	8.2
62.5°	7.2
65°	6.5
67.5°	5.5
70°	4.7
72.5°	4.0
75°	3.2
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)