

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271725

Luminaire Tested: P3AS09R509827DE010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1271725  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R509827DE010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 446.0 lumens  
Efficiency: N/A  
Efficacy: 40.5 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271725  
CATALOG NUMBER: P3AS09R509827DE010 E3DLD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1271725  
 CATALOG NUMBER: P3AS09R509827DE010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	90629
5°	89302
10°	85347
15°	79047
20°	71033
25°	62447
30°	53097
35°	43072
40°	32346
45°	20839
50°	9893
55°	7799
60°	7368
65°	6849
70°	6219
75°	5592
80°	5177
85°	5032

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20839 cd/sqm



TEST NUMBER: P1271725  
 CATALOG NUMBER: P3AS09R509827DE010 E3DLD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.0	8.5
10°-20°	97.1	21.8
20°-30°	118.0	26.4
30°-40°	100.0	22.4
40°-50°	52.0	11.6
50°-60°	18.7	4.2
60°-70°	13.0	2.9
70°-80°	7.0	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	253.1	56.7
0°-40°	353.1	79.2
0°-60°	423.8	95.0
0°-90°	446.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	446.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	413	
5°	406	38
15°	348	97
25°	258	118
35°	161	100
45°	67	52
55°	20	19
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1271725  
CATALOG NUMBER: P3AS09R509827DE010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	413.3
2.5°	411.8
5°	405.7
7.5°	396.5
10°	383.3
12.5°	366.5
15°	348.2
17.5°	327.3
20°	304.4
22.5°	281.0
25°	258.1
27.5°	234.2
30°	209.7
32.5°	185.3
35°	160.9
37.5°	136.9
40°	113.0
42.5°	90.1
45°	67.2
47.5°	44.8
50°	29.0
52.5°	22.4
55°	20.4
57.5°	18.3
60°	16.8
62.5°	14.8
65°	13.2
67.5°	11.2
70°	9.7
72.5°	8.1
75°	6.6
77.5°	5.1
80°	4.1
82.5°	3.1
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)