

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271748

Luminaire Tested: P3AS09R559827DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1271748  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R559827DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 555.0 lumens  
Efficiency: N/A  
Efficacy: 50.5 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271748

CATALOG NUMBER: P3AS09R559827DE010 E3DL1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1271748

CATALOG NUMBER: P3AS09R559827DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 95  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 84  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 68  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 67  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 73  | 63  | 57  | 53  | 72  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 152400 |
| 5°  | 150847 |
| 10° | 145689 |
| 15° | 134666 |
| 20° | 116210 |
| 25° | 91771  |
| 30° | 65099  |
| 35° | 41974  |
| 40° | 25219  |
| 45° | 14203  |
| 50° | 7642   |
| 55° | 2714   |
| 60° | 2456   |
| 65° | 2387   |
| 70° | 2308   |
| 75° | 2118   |
| 80° | 1894   |
| 85° | 1258   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14203 cd/sqm

TEST NUMBER: P1271748

CATALOG NUMBER: P3AS09R559827DE010 E3DL1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 64.5   | 11.6      |
| 10°-20°   | 164.0  | 29.6      |
| 20°-30°   | 171.9  | 31.0      |
| 30°-40°   | 100.3  | 18.1      |
| 40°-50°   | 37.5   | 6.8       |
| 50°-60°   | 8.8    | 1.6       |
| 60°-70°   | 4.6    | 0.8       |
| 70°-80°   | 2.7    | 0.5       |
| 80°-90°   | 0.7    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 400.4  | 72.1      |
| 0°-40°    | 500.7  | 90.2      |
| 0°-60°    | 547.0  | 98.6      |
| 0°-90°    | 555.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 555.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 695 |      |
| 5°  | 685 | 64   |
| 15° | 593 | 164  |
| 25° | 379 | 172  |
| 35° | 157 | 100  |
| 45° | 46  | 38   |
| 55° | 7   | 9    |
| 65° | 5   | 5    |
| 75° | 2   | 3    |
| 85° | 0   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1271748

CATALOG NUMBER: P3AS09R559827DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 695.0 |
| 2.5°  | 693.0 |
| 5°    | 685.3 |
| 7.5°  | 673.1 |
| 10°   | 654.3 |
| 12.5° | 627.8 |
| 15°   | 593.2 |
| 17.5° | 549.4 |
| 20°   | 498.0 |
| 22.5° | 440.4 |
| 25°   | 379.3 |
| 27.5° | 316.7 |
| 30°   | 257.1 |
| 32.5° | 203.2 |
| 35°   | 156.8 |
| 37.5° | 119.1 |
| 40°   | 88.1  |
| 42.5° | 63.1  |
| 45°   | 45.8  |
| 47.5° | 33.1  |
| 50°   | 22.4  |
| 52.5° | 12.7  |
| 55°   | 7.1   |
| 57.5° | 6.1   |
| 60°   | 5.6   |
| 62.5° | 5.1   |
| 65°   | 4.6   |
| 67.5° | 4.1   |
| 70°   | 3.6   |
| 72.5° | 3.1   |
| 75°   | 2.5   |
| 77.5° | 2.0   |
| 80°   | 1.5   |
| 82.5° | 1.0   |
| 85°   | 0.5   |
| 87.5° | 0.5   |
| 90°   | 0.0   |

(END OF REPORT)