

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271800

Luminaire Tested: P3AS09R659827DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659827DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 606.9 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271800
CATALOG NUMBER: P3AS09R659827DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1271800

CATALOG NUMBER: P3AS09R659827DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77	77	77	77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67	67	67	67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63	63	63	63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59	59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162640
5°	151023
10°	146045
15°	140750
20°	130118
25°	118555
30°	91609
35°	53083
40°	21068
45°	8962
50°	2115
55°	268
60°	219
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8962 cd/sqm



TEST NUMBER: P1271800
 CATALOG NUMBER: P3AS09R659827DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	10.7
10°-20°	172.8	28.5
20°-30°	218.6	36.0
30°-40°	124.5	20.5
40°-50°	24.7	4.1
50°-60°	1.3	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.1	75.1
0°-40°	580.6	95.7
0°-60°	606.6	99.9
0°-90°	606.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	742	
5°	686	65
15°	620	173
25°	490	219
35°	198	125
45°	29	25
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1271800
CATALOG NUMBER: P3AS09R659827DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	741.7
1°	736.3
2°	724.3
3°	710.3
4°	696.6
5°	686.1
6°	678.4
7°	672.1
8°	666.6
9°	661.2
10°	655.9
11°	650.2
12°	644.2
13°	637.0
14°	629.2
15°	620.0
16°	609.0
17°	597.0
18°	584.1
19°	570.3
20°	557.6
21°	544.6
22°	532.9
23°	520.7
24°	506.5
25°	490.0
26°	470.3
27°	446.6
28°	419.9
29°	391.5
30°	361.8
31°	329.1
32°	296.6
32.5°	279.9
33°	263.7
34°	230.8
35°	198.3
36°	168.4
37°	138.7
37.5°	123.5
38°	111.3
39°	90.1
40°	73.6
42.5°	45.4
45°	28.9



TEST NUMBER: P1271800
CATALOG NUMBER: P3AS09R659827DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	17.0
50°	6.2
52.5°	1.2
55°	0.7
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)