

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272676

Luminaire Tested: P3AS20R359827D010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1272676  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R359827D010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1151.0 lumens  
Efficiency: N/A  
Efficacy: 42.0 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272676  
CATALOG NUMBER: P3AS20R359827D010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1272676

CATALOG NUMBER: P3AS20R359827D010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	262918
5°	257362
10°	241011
15°	216346
20°	188200
25°	160364
30°	134324
35°	106997
40°	77345
45°	48966
50°	26677
55°	18504
60°	17455
65°	16240
70°	15515
75°	13217
80°	12628
85°	10819

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 48966 cd/sqm



TEST NUMBER: P1272676  
 CATALOG NUMBER: P3AS20R359827D010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.8	9.5
10°-20°	265.2	23.0
20°-30°	303.9	26.4
30°-40°	248.0	21.5
40°-50°	125.0	10.9
50°-60°	46.5	4.0
60°-70°	31.1	2.7
70°-80°	17.2	1.5
80°-90°	5.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.9	58.9
0°-40°	925.9	80.4
0°-60°	1097.4	95.3
0°-90°	1151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1151.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1199	
5°	1169	109
15°	953	265
25°	663	304
35°	400	248
45°	158	125
55°	48	46
65°	31	31
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P1272676  
CATALOG NUMBER: P3AS20R359827D010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1199.0
1°	1197.6
2°	1194.8
3°	1189.1
4°	1180.5
5°	1169.2
6°	1154.9
7°	1140.7
8°	1122.2
9°	1103.7
10°	1082.4
11°	1059.6
12°	1035.5
13°	1008.4
14°	980.0
15°	953.0
17.5°	880.4
20°	806.5
22.5°	731.1
25°	662.8
27.5°	596.0
30°	530.5
32.5°	465.1
35°	399.7
37.5°	334.2
40°	270.2
42.5°	210.5
45°	157.9
47.5°	113.8
50°	78.2
52.5°	56.9
55°	48.4
57.5°	44.1
60°	39.8
62.5°	35.6
65°	31.3
67.5°	27.0
70°	24.2
72.5°	19.9
75°	15.6
77.5°	12.8
80°	10.0
82.5°	7.1
85°	4.3
87.5°	2.8



TEST NUMBER: P1272676  
CATALOG NUMBER: P3AS20R359827D010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)